



## PRODUCT APPLICATION

# REXNORD® 2010 KLEANTOP® BELT

FOR FOOD PROCESSING  
APPLICATIONS




### REDUCE DOWNTIME IN GENERAL CONVEYING APPLICATIONS WITH DIRECT FOOD CONTACT

When your operation needs a versatile plastic modular belt, the 2010 Series KleanTop® offers the solution. Designed with features that can accommodate a variety of product types, the 2010 Series KleanTop is a favorite amongst food processors for its durability, ease in cleaning and reliability in conveying on a wide range of applications.

To achieve strength, a conveyor belt's design often sacrifices areas that allow for thorough sanitation. The 2010 Series KleanTop features an open hinge design and strong Rexnord plastics, enabling you to save time in sanitation and convey heavier loads in applications such as receiving, washing and packaging.

#### 2010 Series KleanTop Key Features & Benefits



**Strong Carrying Surface**  
Enables conveyance of larger product volumes, increasing throughput.

**Open Hinge Design**  
Gives optimal combination of access for sanitation and abrasion resistance.

**Rod Retention Design**  
Requires only a screwdriver for assembly and disassembly. Keeps rod securely in place, reducing risk of product contamination.

#### Key Industries:

- Bakery
- Snack
- Fruit & Vegetable
- Poultry
- Red Meat
- Seafood

#### Key Applications:

- Receiving
- Washing & Draining
- Cutting & Dicing
- Infeeds & Outfeeds
- Freezing
- Packaging



# REXNORD® 2010 KLEANTOP® BELT

## Rexnord 2010 Series KleanTop Belt Information

Belt Type	Belt Material	Standard Rod Material	Temperature Range						Belt Strength		Approximate Weight											
			Fahrenheit			Celsius																
			min	max		min	max		lbs / ft	N/m	lbs/ft <sup>2</sup>	kg/m <sup>2</sup>										
				dry	wet		dry	wet														
2011 Nub Top	BHT (PP)	Polypropylene	40	220	212	4	104	100	800	11,672	1.89	9.23										
	BLT (PE)	Polyethylene	-100	80	80	-73	27	27	500	7,295	2.03	9.91										
	WHT (PP)	Polypropylene	40	220	212	4	104	100	800	11,672	1.89	9.23										
	WLT (PE)	Polyethylene	-100	80	80	-73	27	27	500	7,295	2.03	9.91										
2015 Flat Top	BHT (PP)	Polypropylene	40	220	212	4	104	100	800	11,672	1.89	9.23										
	BLT (PE)	Polyethylene	-100	80	80	-73	27	27	500	7,295	2.03	9.91										
	FTR (PA)	Polyester	-80	220	NR	-62	104	NR	1,000	14,590	2.89	14.11										
	WHT (PP)	Polypropylene	40	220	212	4	104	100	800	11,672	1.89	9.23										
	WLT (PE)	Polyethylene	-100	80	80	-73	27	27	500	7,295	2.03	9.91										
2016 Perforated Top	WSM (POM)	Polyester	-40	180	150	-40	82	66	1,000	14,590	2.89	14.11										
	BHT (PP)	Polypropylene	40	220	212	4	104	100	800	11,672	1.89	9.23										
	FTR (PA)	Polyester	-80	220	NR	-62	104	NR	1,000	14,590	2.89	14.11										
	WHT (PP)	Polypropylene	40	220	212	4	104	100	800	11,672	1.89	9.23										

## Rexnord 2010 Series KleanTop KU2010 TruTrack Thermoplastic Sprocket Information


Number of Teeth		Pitch Diameter		Outside Diameter		Bore Diameter (Shaft Ready)								Bore Diameter (Idler)				Approximate Weight			
						Round				Square				in		mm					
						in	mm	in	mm	in	mm	in	mm	min	max	min	max			min	max
actual	effect	in	mm	in	mm	min	max	min	max	min	max	min	max	min	max	min	max	min	max	lbs	kg
8	8	5.2	132.7	4.8	120.9	3/4	3	20	75	1 1/2	2	40	50	3/4	3	20	75	0.44	0.20		
10	10	6.5	164.4	6.1	153.9	3/4	3 1/2	20	90	1 1/2	2 1/2	40	65	3/4	3 1/2	20	90	1.06	0.48		
12	12	7.7	196.3	7.4	188	1	3 1/2	25	90	1 1/2	3 1/2	40	90	1	3 1/2	25	90	1.59	0.72		
16	16	10.3	260.4	10.3	262.1	1	3 1/2	25	90	1 1/2	4 1/2	40	120	1	3 1/2	25	90	3.62	1.64		




Motion Control Solutions  
Regal Rexnord

Contact us: [rexnord.com/contact](http://rexnord.com/contact)


[regalrexnord.com](http://regalrexnord.com)



2011 Nub Top



2015 Flat Top



2018 Perforated Top

The proper selection and application of products and components, including assuring that the product is safe for its intended use, are the responsibility of the customer. To view our Application Considerations, please visit <https://www.regalrexnord.com/Application-Considerations>.

To view our Standard Terms and Conditions of Sale, please visit <https://www.regalrexnord.com/Terms-and-Conditions-of-Sale> (which may redirect to other website locations based on product family).

"Regal Rexnord" is not indicative of legal entity. Refer to product purchase documentation for the applicable legal entity.

Regal Rexnord, Rexnord, and KleanTop are trademarks of Regal Rexnord Corporation or one of its affiliated companies.

© 2019, 2022 Regal Rexnord Corporation, All Rights Reserved.  
MCSSP22088E • Form# FT5-039E

